
Parts List HYBRIDFLUSH® AEF-801 SERIES


AUTOMATIC/MANUAL FLUSH VALVE SYSTEM FOR WATER CLOSETS (TOILETS) AND URINALS





Advanced Modern Technologies Corporation

19800 Nordhoff Place, Chatsworth, CA 91311 Tel: (818) 883-2682 Toll Free: (800) 874-7822 Fax: (818) 883-2620 www.amtcorporation.com



Parts List

HYBRIDFLUSH® SENSOR OPERATED FLUSH VALVE SYSTEM PARTS					Ball Relief Valves for HYBRIDFLUSH®			
REF	PICTURE	PART #	DESCRIPTION	REF	PICTURE	PART #	DESCRIPTION	
1		SC801	Screw for Top Plastic Cover	17		DI-BRV-U05	Ball Relief Valve Assembly for HYBRIDFLUSH® - Urinal 0.5gpf	
2		PC801	Plastic Cover for Housing			DI-BRV-U10	Ball Relief Valve Assembly for HYBRIDFLUSH® - Urinal 1.0gpf	
3		PH801	Plastic Housing Assembly			DI-BRV-U15	Ball Relief Valve Assembly for HYBRIDFLUSH [®] - Urinal 1.5gpf	
N/S		EMA 801	Electronic Module Assembly			DI-BRV-U18	Ball Relief Valve Assembly for HYBRIDFLUSH® - Urinal 0.125gpf or 1/8gpf	
4	11	SC801	Screw for Plastic Housing			DI-BRV-T11	Ball Relief Valve Assembly for HYBRIDFLUSH® - Water Closet 1.1gpf	
5		AABAT	AA Cell Alkaline Battery (Each)			DI-BRV-T12	Ball Relief Valve Assembly for HYBRIDFLUSH® - Water Closet 1.28gpf	
6		MBA801	HYBRIDFLUSH® Motor & Base Assembly			DI-BRV-T16	Ball Relief Valve Assembly for HYBRIDFLUSH® - Water Closet 1.6gpf	
7		EM801	Electronic Module			DI-BRV-T35	Ball Relief Valve Assembly for HYBRIDFLUSH® - Water Closet 3.5gpf	
8		RC801	Rubber Cover for Electronic Module					
9		BC801	Battery Cover (Metal)					
11		CO801	Top Metal Cover					
12		SWA801	Sensor Window Assembly					
13		AW801	Allen Wrench for Sensor Window Screw					
14	0	WSC801	Cover for Sensor Window Screw					
15-1		LR801S-1	Locking Ring for Sloan Valve Body					
15-2		LR801Z-1	Locking Ring for Zurn Valve Body					
16		WR801	Installation Wrench					

Diaphragm/Repair Kit Reference Chart

	Diaphragm A	ssemblies	for HYBRIDFLUSH®	Silicone Diaphragm Assemblies for HYBRIDFLUSH®			
REF	PICTURE	PART #	DESCRIPTION	REF	PICTURE	PART #	DESCRIPTION
N /S		DI-H-U05	Diaphragm Assembly for HYBRIDFLUSH® - Urinal 0.5gpf	- N/S		DI-SH-U05	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Urinal 0.5gpf
		DI-H-U10	Diaphragm Assembly for HYBRIDFLUSH [®] - Urinal 1.0gpf		0	DI-SH-U10	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Urinal 1.0gpf
		DI-H-U15	Diaphragm Assembly for HYBRIDFLUSH® - Urinal 1.5gpf			DI-SH-U15	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Urinal 1.5gpf
		DI-H-U18	Diaphragm Assembly for HYBRIDFLUSH® - Urinal 0.125gpf or 1/8gpf			DI-SH-U18	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Urinal 0.125gpf or 1/8gpf
		DI-H-T11	Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 1.1gpf	- N/S		DI-SH-T11	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 1.1gpf
N/S		DI-H-T12	Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 1.28gpf		0	DI-SH-T12	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 1.28gpf
		DI-H-T16	Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 1.6gpf			DI-SH-T16	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 1.6gpf
		DI-H-T35	Diaphragm Assembly for HYBRIDFLUSH [®] - Water Closet 3.5gpf			DI-SH-T35	Silicone Diaphragm Assembly for HYBRIDFLUSH® - Water Closet 3.5gpf
	Diaphragm I	Repair Kits	for HYBRIDFLUSH®	Silicone Diaphragm Repair Kits for HYBRIDFLUSH®			
REF	PICTURE	PART #	DESCRIPTION	REF	PICTURE	PART #	DESCRIPTION
		DI-RKH-U05	Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 0.5gpf	· N/S		DI-SRKH-U05	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 0.5gpf
N/S		DI-RKH-U10	Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 1.0gpf			DI-SRKH-U10	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 1.0gpf
14/3		DI-RKH-U15	Diaphragm Repair Kit for HYBRIDFLUSH [®] - Urinal 1.5gpf			DI-SRKH-U15	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 1.5gpf
		DI-RKH-U18	Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 0.125gpf or 1/8gpf			DI-SRKH-U18	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Urinal 0.125gpf or 1/8gpf
		DI-RKH-T11	Diaphragm Repair Kit for HYBRIDFLUSH [®] - Water Closet 1.1gpf	- N/S		DI-SRKH-T11	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Water Closet 1.1gpf
N/S		DI-RKH-T12	Diaphragm Repair Kit for HYBRIDFLUSH® - Water Closet 1.28gpf			DI-SRKH-T12	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Water Closet 1.28gpf
		DI-RKH-T16	Diaphragm Repair Kit for HYBRIDFLUSH® - Water Closet 1.6gpf			DI-SRKH-T16	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Water Closet 1.6gpf
		DI-RKH-T35	Diaphragm Repair Kit for HYBRIDFLUSH [®] - Water Closet 3.5gpf			DI-SRKH-T35	Silicone Diaphragm Repair Kit for HYBRIDFLUSH® - Water Closet 3.5gpf

HYBRIDFLUSH® Accessories (SOLD SEPARATELY)

Push Button Conversion Kit (PBCK)

The Push Button Conversion Kit (PBCK) includes a push button and spring that replaces the existing flush handle and spring to convert it into a mechanical push button.

By using the push button with the HYBRIDFLUSH® system the user is able to flush the urinal or toilet manually even when the batteries on the HYBRIDFLUSH® system are drained. Installation of the push button also solves the "handle kicking problem" usually associated with flushometer handles therefore reducing maintenance from leaky seals and extending the life of the flushometer.






Push Button Complete (PB-C)


The Push Button Complete Assembly (PB-C) includes all the necessary parts of the push button that replaces the existing cap to convert it into a mechanical push button. Normally, the PB-C is used when changing from an existing automatic flush valve that requires the handle area to be capped off.

By using the push button with the HYBRIDFLUSH® system the user is able to flush the urinal or toilet manually even when the batteries on the HYBRIDFLUSH® system are drained. Installation of the push button also solves the "handle kicking problem" usually associated with flushometer handles therefore reducing maintenance from leaky seals and extending the life of the flushometer.



Handle Cover (HC801)

The Handle Cover (HC801) is used to cap off handle area when the manual handle or the push button is not desired.



Warranty

AMTC WARRANTS ITS PRODUCTS TO BE FREE OF DEFECTS IN MATERIAL AND WORKMANSHIP FOR A PERIOD OF FIVE (5) YEARS FROM DATE OF PURCHASE, WHEN PROPERLY INSTALLED AND UNDER NORMAL USE AND SERVICE. THESE PROVISIONS DO NOT INCLUDE THE BATTERIES SHIPPED WITH THE PRODUCTS. A DEFECTIVE PRODUCT MAY BE RETURNED TO AMTC OR ITS AUTHORIZED REPRESENTATIVES WITHIN FIVE (5) YEARS FROM DATE OF PURCHASE WITH THE PROPER INVOICE OF PURCHASE. AMTC, AT ITS DISCRETION, WILL REPLACE OR REPAIR DEFECTIVE PRODUCT AT NO CHARGE. CLAIMS FOR LABOR, TRANSPORTATION, AND ANY OTHER INCIDENTAL COSTS WILL NOT BE ALLOWED. AMTC WILL NOT BE RESPONSIBLE FOR ANY CONSIDERABLE DAMAGES OF ANY KIND WHATSOEVER.

FOR TECHNICAL SUPPORT PLEASE CALL TOLL FREE 1-800-874-7822 OR VISIT OUR WEBSITE AT WWW.AMTCORPORATION.COM

MAKE SURE TO VISIT OUR WEBSITE PERIODICALLY FOR INFORMATION ON NEW PRODUCTS AND TO DOWNLOAD ANY IMPORTANT PRODUCT DOCUMENTS THAT YOU MAY NEED IN THE FUTURE.



Advanced Modern Technologies Corporation

19800 Nordhoff Place, Chatsworth, CA 91311 Tel: (818) 883-2682 Toll Free: (800) 874-7822 Fax: (818) 883-2620 www.amtcorporation.com